

## 3.5" SMILE MONITOR FLUSH BOX

**Reference:** 06546

In order to install the Smile monitor, it is necessary to fit a box into the wall where the monitor is to be installed. This will allow perfect integration with any setting. A decorative frame must...

### DESCRIPTION

In order to install the Smile monitor, it is necessary to fit a box into the wall where the monitor is to be installed. This will allow perfect integration with any setting. A decorative frame must also be added.

The flush boxes have some marks cut into the base and side which will open with a light blow or pressure, thereby allowing the passage of cables.

Available for the 7" and 3.5" Smile monitors. Select the box according to the size of the monitor.

Once fitted into the flush box, the monitor will protrude 4mm from the wall.

### TECHNICAL SPECIFICATIONS

Accessories for installation:

Decorative frame for Smile 7" Monitor.

Frame measurements: 209x196x4mm (horizontal-vertical-depth).

Flush box for Smile 7" Monitor.

Box measurements: 198x186x44mm (horizontal-vertical-depth).

Decorative frame for Smile 3.5" Monitor.

Frame measurements: 127x196x4. (horizontal-vertical-depth).

Flush box for Smile 3.5" Monitor.

Box measurements: 112x186x44.

**Weight:** 0,150 kg

**Size of product when packed:** 4,6x19x12 cm

**EAN 13:** 8424299065465